


Rubber Ramp Miter Returns

- Made from molded styrene butadiene rubber
- Glue miter returns to each end using an adhesive such as **RR200**
- Miter Returns are supplied in pairs: one left-hand (**RR12LH**) and one right-hand (**RR12RH**)
- If only one miter return is required, specify the handing

RR12_H



Recycled Rubber Ramp Assembly

- ADA Compliant, based on application
- Meets: UL410, ASTM D2047, Federal Specification P-F-430C
- Recycled Rubber Ramp Assemblies meet **IBC/ANSI A117.1-2010**
- Made from #20 mesh minus crumb rubber (with urethane binders) reclaimed from 100% recycled rubber automotive tires
- PEMKO strongly recommends using **RR200** to glue rubber ramps to floor surfaces. Avoid Liquid Nails with Rubber Ramps
- Using ordinary tools, trim to fit your application
- Can be ripped for offsets less than 1 1/4"
- Plane bottom surface of ramp to accommodate irregular surface conditions
- Miter returns are molded into the design of the Recycled Rubber Ramp
- 36" and 60" ramps are supplied as one (1) piece assemblies
- 48" and 72" ramps are supplied as two (2) piece assemblies

Ordering Chart

Other sizes are available, please contact PEMKO customer service.

| PART # | WIDTH "A" (door opening) | WIDTH "B" (total width) |
|-------------|-----------------------------|----------------------------|
| RR1.25FMR36 | 36" | 41" |
| RR1.25FMR48 | 48" | 53" |
| RR1.25FMR60 | 60" | 65" |
| RR1.25FMR72 | 72" | 77" |
| RR1.25FMR96 | 96" | 101" |

